

INSTALLATION INSTRUCTIONS


SLENDERFORM LUMINAIRE TO RND/SQ POLE



IMPORTANT : READ ALL INSTRUCTIONS BEFORE PERFORMING ANY WORK. BE SURE ALL POWER IS OFF PRIOR TO INSTALLING LUMINAIRES.

WARNING: FIXTURE MUST BE GROUNDED IN ACCORDANCE WITH APPROPRIATE CODES. FAILURE TO DO SO MAY RESULT IN SERIOUS INJURY.

NOTE: THIS INSTALLATION INSTRUCTION SHEET IS FOR THE AUTOMATIC PROFILE DIMMING POLE MOUNTING INSTRUCTIONS ARE PROVIDED WITH MOUNTING HARDWARE



1. LOCATED ON THE BOTTOM OF ARM ASSEMBLY, LOOSEN (2) SCREWS TO OPEN DOOR.

2. INSERT BOLSTER PLATE INTO THE INSIDE OF POLE WITH TAPPED HOLE TOWARD THE BASE. POSITION LUMINAIRE SO THE TOP MOUNTING HOLE IS ALIGNED WITH THE TOP HOLE ON THE POLE. INSTALL LOCK WASHER AND 1.00" FLAT WASHER TO THE 3/8-16 X 1-1/2" HEX HEAD BOLT THROUGH THE TOP MOUNTING HOLE. INSTALL SPLIT LOCK WASHER AND NUT TO THE END OF THE TOP BOLT.

3. NOTES: SQUARE POLES: USE SQUARE POLE ADAPTER BETWEEN LUMINAIRE AND POLE.

4. THREAD 3/8-16 X 1-1/2" HEX HEAD BOLT WITH LOCK WASHER INTO THE BOTTOM TAPPED HOLE IN THE BOLSTER PLATE. TIGHTEN THE TWO BOLTS TO 18 FT-LBS.

5. CONNECT SUPPLY WIRES AND GROUND WIRES TO THE LUMINAIRE TERMINAL BLOCK AND GROUND LUG.

6. SECURE THE SUPPLY WIRES WITH THE CABLE TIE (STRAIN RELIEF) ON THE BOLSTER PLATE AND IN THE ARM.

7. INSTALL PHOTO CONTROL IF USED.

8. CLOSE DOOR AND SECURE IT BEING CAREFUL NOT TO OVER TIGHTEN SCREWS.

9. ENERGIZE LUMINAIRE TO TEST INSTALLATION.



© 2016 Philips Lighting Holding B.V. All rights reserved.
www.philips.com/luminaires

443561200920 Rev. A
Page 1 of 1

Philips Lighting North America
Cooperation
200 Franklin Square Drive,
Somerset, NJ 08873, USA

Philips Lighting Canada Ltd.
281 Hillmount Road.
Markham, ON, Canada L6C 2S3