

PHILIPS

Wall light

myGarden

Dusk

grey

LED



17808/87/16



Turn sunlight into LED light

Capture the sun's energy with Philips myGarden Dusk wall light. The high-capacity solar panel and efficient LEDs combine for long-lasting light. The ingenious design offers subtle style and beautiful light, and a motion sensor.

Sustainable light solutions

- High quality LED light
- Warm white light
- Solar energy
- Maximum light duration: 6 hours
- Philips offers 5 year warranty on the LED module and driver

Special characteristics

- On/off switch on article

Designed for your garden

- Motion sensor included, for convenience and reassurance
- Unique day/night function
- IP44 - weather proof
- Integrated solar panel
- No power cables required


Highlights

High quality LED light




The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Warm white light




Light can have different color temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

Solar energy



Philips myGarden Solar lights are designed to make the most of the energy they receive from the sun, for light that lasts longer. With no electricity consumption at all, it helps you save money on your electricity bills and do your bit for the environment.

Maximum light duration: 6 hrs



Philips myGarden Solar lights are designed to make the most of the energy they receive from the sun, for light that lasts longer. Both the solar panel and LED light are of the highest quality to maximize sunlight collection. The length of lighting time depends on the amount of sunlight the solar panel receives. In good weather conditions, this light has a maximum light duration of 6 hours. Furthermore, energy-saving features such as an on/off switch or a motion sensor help to ensure that whatever the weather or time of year, you'll always be able to light your outdoor areas brightly.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

On/off switch on article



With the button discreetly integrated onto the lamp, you can easily switch the light on and off.

Motion sensor included




A motion sensor is included to welcome you when you return home or let you know when someone has arrived. When the sensor detects movement, the lamp switches on automatically.

Unique day/night function



Thanks to the day/night function, this outdoor light automatically switches on when it gets dark outside. Use this unique function for long summer evenings or for safety reasons.

Integrated solar panel



This Philips myGarden Solar light has an integrated solar panel as part of the light. The light is free of cables and emits up to 100 lumens of light, enough to illuminate a defined area or highlight a feature.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

No power cables required



Philips myGarden Solar takes the hard work and hassle out of outdoor installation, requiring just a few simple minutes to place in your garden ✓ even if you've never installed outdoor lighting before. With no mains power cables to worry about, there is lots of flexibility for placement, since you don't need to be close to a power socket.

Specifications

Design and finishing

- Color: grey
- Material: aluminium, synthetics

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion & day-and-night sensor: Yes
- Solar Energy: Yes

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Wall light
- EyeComfort: No

Product dimensions & weight

- Height: 13.6 cm
- Length: 16.1 cm
- Net weight: 0.590 kg
- Width: 16.1 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Light source equivalent to traditional bulb of: 11 W
- Total lumen output fixture: 100 lm
- Bulb technology: LED, Safety Extra Low Voltage
- Light color: warm white
- Mains power: 3.7 V
- LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 1 W
- IP code: IP44, protection against objects bigger than 1 mm, protection from splashed water
- Class of protection: III - safe extra low voltage

Packaging dimensions and weight

- EAN/UPC - product: 8718291489443
- Net weight: 0.590 kg
- Gross weight: 0.796 kg
- Height: 178.000 mm
- Length: 153.000 mm
- Width: 173.000 mm
- Material number (12NC): 915004347702
- Net Weight: 0.590 kg



Issue date: 2020-07-02
Version: 0.513

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com