


3-3/4" Aperture Premium Die-Cast Step Baffle

Ceiling Opening: 3-3/4" (95mm)



Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

Reflector Trim	Frame-in Kit		Lamp		
2005BK Black	2002	Frame Non-IC	50W PAR20	75W PAR16,R20	60W A19
2005WB White	2003RS	Remodeler Ring Non-IC	50W PAR20	75W PAR16,R20	60W A19
	2002AIC	Frame IC AirSeal®	50W PAR/R20	45W PAR16	

Features

Reflector: Hydroformed aluminum. .032" thick ; Anobrite (anodic-processed) semi-specular finish for permanent reflectivity; white trim flange.

Step Baffle: Die-cast aluminum with stepped conical surface for low brightness, black or white finish.

Frame-in Kit

See Frame-In Kit specification sheets for more details.

Finish

All painted finishes are baked powder or enamel.

Accessories

1967C 2 in. Thick Ceiling Adaptor.

Markings

cULus listed, suitable for damp locations.

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	