

LUMEC

by @signify

Urban

Serenade

S23-S29-S50-S51 Post Top



Evokes memories of the lighting of the past, having the appearance of a gently glowing acorn. The **Serenade** is a beautiful staple of elegance and subtlety with a mighty and brilliant heart. It can be used to accentuate any environment no matter how harsh the prevailing conditions might be. The **Serenade** is a straightforward, practical luminaire, designed for performance and reliability.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Mounting & Configuration	Pole*	Finish**
S50-PCFC	100 HPS	RR5	120	FS	CRA-1A	R890A-15	BKTX

* Consult the eCatalog for details and the complete line of poles.

The specially formulated Lumital powder coat finish is available in a range of many standard colors.

** Consult LumeC's Color Chart for complete specifications.

Luminaires

Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.

S23



S23-CB



S23C1



S23C2-CUC




These globes are available with the following finish:

- PCFC** Frosted clear polycarbonate
- PCFO** Frosted opal polycarbonate
- ACFC** Frosted clear acrylic

S29




S50-FNC



S50C1-BSTC-BSC



S50C2



S51-CPTC



S23-S29-S50-S51 Serenade

Post Top

Lamp/HID

Wattage	RR3 / RR3MD / RR5		SE3 / SE5		RACE3 / RACE3D / RACE5	
Luminaire	S23 S23C1 / S23C2 S50 S50C1S S50C2	S29 S51	S50 S50C1 S50C2	S51	S50 S50C1 S50C2	S51
50 MH, medium	■	■	■	■	■	■
70 MH, medium	■	■	■	■	■	■
100 MH, medium	■	■	■	■	■	■
150 MH, medium	■	■	■	■	■	■
200 MH, mogul	■	N/A	■	N/A	■	■
250 MH, mogul	■	N/A	■	N/A	■	■
250 PSMH, mogul	■	N/A	■	N/A	■	N/A
35 HPS, mogul	■	■	■	■	■	■
50 HPS, mogul	■	■	■	■	■	■
70 HPS, mogul	■	■	■	■	■	■
100 HPS, mogul	■	■	■	■	■	■
150 HPS, mogul	■	■	■	■	■	■
200 HPS, mogul	N/A	N/A	■	■	■	N/A
250 HPS, mogul	N/A	N/A	■	■	■	N/A

■ Available. N/A : Not available.

Optical System / HID

(Lamps not included)



RR Optics (All)
Round borosilicate refractor
Luminous center:
23-3/8" (584 mm)

RR5 Symmetrical
RR3 Asymmetrical
RR3MD Asymmetrical with medium deflector



SE Optics
(S50/S50C1/S50C2/S51)
Hydro-formed cut-off reflector system set in faceted arc-image duplicating patterns
Luminous center:
24-7/8" (584 mm)

SE5 Symmetrical
SE3 Asymmetrical
> House shield available in option (HS)



RACE Optics
(S50/S50C1/S50C2/S51)
Round acrylic (max. 100W) or borosilicate (150W and more) refractor with segmented uplight recovery dome
Luminous center:
27-1/2" (698 mm)

RACE5 Symmetrical
RACE3 Asymmetrical
RACE3D Asymmetrical with deflector

Lamp/QL

Wattage	SE5 ¹	LMP ²
55 QL	■	■
85 QL	■	■

■ Available

1. S50 / S50C1 / S50C2 / S51.

2. S23 / S23B / S23BC1 / S23BC2 / S29.

(LMP: Lamp without optical system)

High frequency generator for induction lamp (4000K).

Instant start. Operating range 50-60 Hz or DC.

Lamp minimum starting temperature -40F (-40 °C).

(Lamps included)

Voltage / QL

QL
120
208
240
277

Voltage / HID

HID ¹
120
208
240
277
347
480

1. Multi-top ballast also available.

Options


BC Block connector (all)
TN3 Adaptor to fit over a 3" (76 mm) O.D. by 4" (102 mm) long tenon (all)
TN3.5 Adaptor to fit over a 3 1/2" (89 mm) O.D. by 4" (102 mm) long tenon (all)
FNC Copper-colored painted finial (all)
FS Fusing (consult factory) (all)
PH8 Photoelectric cell (all)
CB Painted decorative band, color to be specified (see standard Lumec Color Chart) (S23B)
BS Brass decorative band (S23C1/S50C2/S50C1/S50C2)

BSC Brass decorative band, protected by a polyester clear coat (S23C1/S50C2/S50C1/S50C2)
CU Copper decorative bands, located on the arms of the gard (S23C1/S50C2/S50C1/S50C2)
CUC Copper decorative band, protected by a polyester clear coat (S23C1/S50C2/S50C1/S50C2)
CPT Copper cupola (S50/S50C1/S50C2/S51)
CPTC Copper cupola, protected by a polyester clear coat (S50/S50C1/S50C2/S51)
HS House shield, for SE optic only (S50/S50C1/S50C2/S51)
BST Brass decorative cupola (S50/S50C1/S50C2/S51)
BSTC Brass decorative cupola, protected by a polyester clear coat

S23-S29-S50-S51 Serenade



Post Top

Finials




Mountings

Consult the eCatalog for details and the complete line of mountings.



Poles and Pole Options

Consult the eCatalog for details and the complete line of poles.



S23-S29-S50-S51 Serenade

Post Top

Assembly examples

