

Day-Brite


CFI

by  Signify

Linear

Valueline SL
undercabinet

T5



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Day-Brite / CFI Valueline SL undercabinet is an economical T5 luminaire with electronic ballast. It is available in 12", 21", 24", 33", and 42" lengths.

Ordering guide

Example: SL281-120-EB-LP

Family	Lamping	Voltage	Ballast	Options
<input type="text" value="SL"/>	—	<input type="text" value="120"/> —	<input type="text" value="EB"/> —	<input type="text" value="LP"/>
SL	18 1-8WT5 (12.25") 113 1-13WT5 (21.25") 28 2-8WT5 (24.50") 281 1-8WT5/1-13WT5 (33.50") 213 2-13WT5 (42.50")	120 120V	EB Electronic ballast	LP Lamp provided (4100K)

Replacement Lenses (order separately)

Lens cat. #	Product
• LSL12	SL18
• LSL21	SL113
• LSL24	SL28
• LSL33	SL281
• LSL42	SL213



SL Valueline undercabinet

T5


Construction/Finish

- Finish is baked white enamel.
- “L” shaped lens (luminous front) is white acrylic.
- 1-1/8” ultra slim styling creates an unobtrusive hidden light source.

Electrical

- All units include electrical fitting to accept flexible conduit or romex.
- Rocker switch and convenience outlet supplied, shipped loose.
- cULus listed for damp locations.
- 841 4100K color temperature T5 lamp included.
- Available with 120V electronic ballast only.

Dimensions



Some luminaires use fluorescent or high intensity discharge (HID) lamps that contain small amounts of mercury. Such lamps are labeled, “Contain Mercury” and/or the symbol “HG”. Lamps that contain mercury must be disposed of in accordance with local requirements. Information regarding lamp recycling and disposal can be found at www.lamprecycle.org

