

## **SmartBright**



**Trusted** 



Reliable



Great value





# SmartBright Weatherproof Batten

Real professionals choose Philips SmartBright for their everyday lighting installations.

#### Trusted performance, everyday.

Available in both 600mm and 1,200mm lengths, the new tri-colour/dual power weatherproof batten is an ideal replacement for 1x18W and 1x36W T8 weatherproof battens.

The new range offers high efficacy and high output of bespoke quality light, plus an excellent service life and warranty - making it an ideal and flexible choice for your outdoor applications.

#### Features and benefits

- ✓ Available in 600mm and 1.200mm lengths
- ✓ 3 colour temperatures and dual power settings in each part number
- ✓ Quick clip cover removal fast and easy installation
- ✓ Long service life with excellent reliability
- ✓ High degree of protection for outdoor applications (IP65/IK08)

#### **Applications**

- All general outdoor building applications
- ✓ Commercial, office and industrial properties
- ✓ Factories, parking garages, correctional facilities, underpasses, airports etc.

#### **Product highlights**












#### **Product data**

	WT067C SWT SCCT LED L600 PSU AU	WT067C SWT SCCT LED L1200 PSU AU			
Power (selectable)	10/20W	20/40W			
System lumens	1000/2000lm	2000/4000lm			
System efficacy	100lm/W				
CCT (Selectable)	4000/5000/6500K				
CRI	> 80				
SDCM	4000K and 6500K: SDCM < 5; 5000K: SDCM < 7				
Beam angle	110°				
IP / IK rating	IP65/IK08				
Operating temperature	-20°C to +40°C				
Lifetime	50,000 hrs (L70)				
Input voltage	220-240V, 50/60Hz				
Power factor	> 0.9				
Electrical class	Class I				
Driver	Fixed Output				
Mounting type	Surface mount with bracket				
Housing colour	RAL7035 light grey				
Material	Housing: Polycarbonate (PC)	Diffuser: Polycarbonate (PC)			
Dimensions	L 656mm x W 107mm x H 72mm	L 1,265mm x W 107mm x H 72mm			
Weight	1kg	1.8kg			

### **Dimensions**



## **Order information**

Order code	Barcode	Power (W)	Light Output (lm)	ССТ (K)	Length (mm)
WT067CSWTL600P	8710163344300	10/20	1000/2000	4000/5000/6500	600
WT067CSWTL1200P	8710163344317	20/40	2000/4000	4000/5000/6500	1,200

