





LUMISTEP



DYNADIMMER



RF / CTC



Philips Iridium gen3 Mini BGP 381

Mounting instructions

Instructions de montage
Montageanleitung
Montage instructie
Instruzioni di montaggio

Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergəsi
Οδηγίες συναμολογησης
Instrukcja montazu

Szerelési utasítások
Návod k montáži
Инструкция по монтажу
Návod k montáži

220 V
240 V

1451

IP66

EN 60598

IK09


16m
max

R&TTE
RED

min
-30°C


max
35°C

	LINE	W +/- 10%				Inrush current	MCB B 16A	DRIVER
LED	GRN11/740	8.9	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN11/830	9.9	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN13/740	10.6	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN13/830	11.6	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN15/740	12.5	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN15/830	13.4	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN17/740	14.2	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN17/830	15.5	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN19/740	14.4	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN19/830	15.5	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN20/740	16.9	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN20/830	18.5	●	●	6.9	15A/320μs	23	22W FP / 22W SR
LED	GRN22/740	16.3	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN22/830	18	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN25/740	18.7	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN25/830	20.7	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN30/740	23.2	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN30/830	25.2	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN35/740	27.1	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN35/830	30.1	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN40/740	31.8	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN40/830	34.8	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP
LED	GRN45/740	36.7	●	●	6.9	21A/300μs	20 / 21 / 24	40W FP / 40W SR / 40W LP





4427 101 41504
© 01/2019 Signify Holding. All rights reserved
Data subject to change without notice
Printed in Poland
www.philips.com/lighting





PHILIPS



2 Version without cable




2' Version with cable




SRG10

10kV protection


10A max.



Version SRG10 without cable







Version SRG10 with cable




Disconnect before servicing
Mettre hors tension avant intervention
Öffnen nur spannungsfrei
Demonteren voor onderhoud

Togliere tensione prima di fare manutenzione
Desconectar antes de manipular
Bryt strömmen före lampbyte

CityTouch OLC NEMA SR



✗ check power
✓ green LED



© 2019 Signify Holding.

All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding.
The Netherlands

4427 101 41504

© 01/2019 Signify Holding. All rights reserved

Data subject to change without notice

Printed in Poland

www.philips.com/lighting