


HADCO

by @signify

Landscape

DWC1

DWC1 Beacon



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Ordering Guide

Example: DWC1 A

| Product Code | DWC1 | Beacon |
|--------------|------|--------|
| Finish | A | Black |

Spacing Chart

Specifications

HOUSING:

Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Single-piece molded silicone gasket to prevent water, dust, and insect filtration. Fasteners are 300 series stainless steel. Two (2) ½" conduit inlets at bottom. Note: Watertight connectors and potting compound (by others) must be used to maintain a watertight seal at conduit entry points.

FINISH:

Composite is textured, pressure formed, molded-in-color.

OPTICAL ASSEMBLY:

Frosted borosilicate glass.

LAMPING:

20W maximum T3 bi-pin lamp. Lamp is included with fixture. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 120VAC, 60Hz input to step-down transformer. 12VAC output to fixture, for use with low voltage lamps. Fixture is pre-wired with 18 AWG black, white, and ground wires.

WARRANTY:

Ten-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height :

8 3/16" (224mm)

Width:

4 15/16" (126mm)

Max. Weight:

2.5 lb.

@signify