

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: 39-4 ABS 18

Product Code	39-4	Banner Arm
<b>Finish</b>	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
<b>Length</b>	18 24 30 36	18" 24" 30" 36"

### Specifications

#### CONSTRUCTION:

Solid cast aluminum ladder rest. Cast aluminum bracket. Turned aluminum knob. 24 1/2" long 7/8" dia. heavy wall pipe threaded and welded to cast aluminum bracket. 4" dia. post order separately.

#### FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

#### Height:

2 5/8"

#### Width:

36 1/4"

