

# KEENE

by  signify

Floodlights

Slim Flood

TF10/30/50/100/150/200



## Illuminate with style

The Keene LED Slim Flood is your best value for discreet and modern design on your floodlighting projects.

Versatile and stylish with six different sizes to choose from, Slim Flood provides application flexibility for ground, wall, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications. The discreet low profile design will not interfere with your landscape layouts.

**Energy savings don't get better than this – up to 85% savings compared to HID\*.**

\* Based on comparison between 50W PSMH luminaires (at 68W) and TF10-NW-G1-K-FL-8-BZ (at 10W).



# Slim Flood LED








## Shine light where you need it

- Complete family of LED floodlights ideal for illuminating signs, building facades or other dark areas.
- Can be mounted on the ground, wall, or pole-mounted.
- Low profile design with durable construction
- All sizes arrive fully assembled and ready to install. All sizes have a yoke mount and the three smaller sizes have a unique Yoke/Knuckle combo mount.
- Fade-resistant, textured bronze finish with tempered glass lens that is heat and impact resistant.
- IP65 rated.




## Ordering guide

example: TF200-NW-G1-Y-FL-8-BZ

Luminaire	LED Color	Generation	Mounting	Distribution	Voltage	Finish
						
<b>TF10</b> LED Slim Flood 10W <b>TF30</b> LED Slim Flood 30W <b>TF50</b> LED Slim Flood 50W <b>TF100</b> LED Slim Flood 100W <b>TF150</b> LED Slim Flood 150W <b>TF200</b> LED Slim Flood 200W	<b>NW</b> Neutral White 4000K, 80CRI	<b>G1</b> Generation 1	<b>K</b> <sup>1</sup> Knuckle Mount (½" NPS male) & Yoke Mount combination  <b>Y</b> <sup>2</sup> Yoke Mount only	<b>FL</b> Flood	<b>8</b> 120-277VAC	<b>BZ</b> Bronze

1. **K** Knuckle Mount and Yoke Mount combination available with TF10 / TF30 / TF50.

2. **Y** Yoke Mount only available with TF100 / TF150 / TF200.



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.