



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering Guide

Example: GAL3 SS S7

<b>Product Code</b>	GAL3	Stainless Steel Pathlyte
<b>Finish</b>	SS	Stainless steel (MATTE FINISH)
<b>Mounting</b>	S7	Mounting Stake

### Specifications

**HOUSING:**

Stainless Steel. Tool-less lamp access. Easy access to lamp. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

**FINISH:**

Linear machine brushed, satin appearance.

**OPTICAL ASSEMBLY:**

Reflector is Stainless Steel.

**LAMPING:**

12W maximum wedge base T3-1/4 lamp. 10W wedge base T3 1/4 (xenon) lamp is included with fixture. Lower wattage lamps are acceptable.

**ELECTRICAL ASSEMBLY:**

Wedge base socket type (T3-1/4 or T5). Socket is hinged for easy relamping. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

**WARRANTY:**

Ten-year limited warranty.

**CERTIFICATIONS:**

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

**Height :**

22 3/8" (568mm)

**Width:**

6 1/8" (156mm)

**Max. Weight:**

3.8 lb

