

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: 39-5 ABS 18

Product Code	39-5	Banner Arm
<b>Finish</b>	ABS	Antique Brass
	ACP	Antique Copper
	ARD	Antique Red
	ASI	Antique Silver
	BLK	Black
	BRN	Brown
	BRZ	Bronze
	FGN	Forest Green
	GRA	Granite
	IRN	Ironstone
	RBZ	Rustic Bronze
	SRT	Shadow Rust
	VBZ	Verde Bronze
	VCP	Verde Copper
	VGN	Verde
VTC	Vintage Copper	
WBZ	Weathered Bronze	
WHT	White	
<b>Length</b>	18	18"
	24	24"
	30	30"
	36	36"

### Specifications

#### CONSTRUCTION:

Solid cast aluminum ladder rest. Cast aluminum bracket. Turned aluminum knob. 24 1/2" long 7/8" dia. heavy wall pipe threaded and welded to cast aluminum bracket. 5" dia. post order separately.

#### FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

#### Height:

3"

#### Width:

37 3/8"

