

# PHILIPS

Suspension light

myLiving


Pods

white

LED



36288/31/CO



## Decorate your home with light

Bring stunning effects to your living room with a suspension light that adds a touch of modern playfulness, with the light either on or off.

### Light effect

- Warm white light for a cozy atmosphere
- Premium glass diffuser for a soft glow

### Durability

- Long life LED light source

# Highlights

## Warm white light for a cozy atmosphere

Perfect for winding down after a long day in front of a film or over dinner.

## Premium glass diffuser for a soft glow

Provides a soft glow for relaxation and focus without distracting glare.

## Long life LED light source

Provides you with a long term lighting investment which offers equal quality light years down the line.

# Specifications

## Design and finishing

- Color: white
- Material: metal

## Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Contemporary
- Type: Suspension light
- EyeComfort: No

## Product dimensions & weight

- Height maximum: 150 cm
- Height minimum: 50 cm
- Length: 40 cm
- Net weight: 4.000 kg
- Width: 40 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 800 lm
- Mains power: Range 100 V – 240 V, 50-60 Hz
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: I – earthed
- Light source replaceable: No

## Design and finishing

- Color: white
- Especially designed for: Living- & Bedroom
- EAN/UPC – product: 6947830433148
- Warranty: 1 year(s)
- Net weight: 4.000 kg
- Material: metal
- Style: Contemporary
- Gross weight: 7.400 kg
- Type: Suspension light
- Height: 505.000 mm
- Lifetime up to: 15,000 hour(s)
- EyeComfort: No
- Length: 143.000 mm
- Height maximum: 150 cm
- Width: 483.000 mm
- Height minimum: 50 cm
- Material number (12NC): 915005395201
- Length: 40 cm
- Net weight: 4.000 kg
- Width: 40 cm
- Total lumen output fixture: 800 lm
- Mains power: Range 100 V – 240 V, 50-60 Hz
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: I – earthed
- Light source replaceable: No



Issue date: 2023-11-08  
Version: 0.180

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)