

PHILIPS

Ceiling light


myLiving

39097 Thallus

gold

LED

39097/10/C5



Your desired ambiance, at your fingertips

Create the right ambience every time. With just a couple of clicks on the remote control, Philips LED ceiling light gives you the flexibility and convenience to choose between a range of light settings for every moment.

Specifications

Design and finishing

- Color: gold
- Material: metal

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Contemporary
- Type: Ceiling light
- EyeComfort: Yes

Product dimensions & weight

- Height: 13.8 cm
- Length: 52 cm
- Net weight: 3.700 kg
- Width: 52 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 1700 lm
- Mains power: Range 220 V – 240 V
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Number of bulbs: 1
- Wattage bulb included: 40 W
- Maximum wattage replacement bulb: 40 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II – double insulated
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC – product: 6947830435890
- Net weight: 3.700 kg
- Gross weight: 6.910 kg
- Length: 0.000 mm
- Width: 0.000 mm
- Material number (12NC): 915005513001



Issue date: 2023-11-08
Version: 0.192

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com