


# PHILIPS

## CoreLine Tempo Small

BVP110



220V  
240V

50Hz  
60Hz




IK08

IP65


Ta  
35°C

>0m

	Flux(lm)	Power(W)	Beam	m <sup>2</sup>	kg
BVP110 LED42/NW A	4200	38.5	Asymmetric	0.052	2.24
BVP110 LED42/NW S	4200	38.5	Symmetric	0.052	2.24




	Ipeak	Ipeak T(@50% of Ipeak)
220 Vrms	4.9A	0.05ms
230 Vrms	5.0A	0.06ms
240 Vrms	5.1A	0.07ms
MCB	Units Max. 38.5W	
B-16 A	95	
C-10 A	59	
C-16 A	95	






Install the luminaire according to the national regulations.


In case of using only the central hole fixation and if the luminaire is higher >3 m, the use of 2nd fixing security system is needed.




1a




1b




2a




adjust the angle by incrementing of 5 degree



2b





2c





2c

### PSU

Mains M20 cable gland that accepts cable diameter from 10 to 14 mm with an external 3 poles quick connector (IP68 rated connector). No need to open the luminaire for the electrical connection.



Cable: 60245IEC57  
Min. 3x1,0 mm<sup>2</sup>  
Max. 3x2,5 mm<sup>2</sup>  
Ø 6.5 - Ø 7.5 mm




3







# glass maintenance instruction.




The luminaire power should be switched off before opening.



4a



4b



- The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
- The luminaire shall be installed or maintained by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.
- Outdoor use only.



© 2016 Philips Lighting Holding B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.  
The Netherlands