
# LIGHTOLIER

by (signify

## Downlighting

### Uniframe CFL 3 3/4"

## 2001F 1 Light Non-IC Frame



Complete Fixture consists of Frame-In Kit and Reflector Trim. Select each separately.

#### UniFrame™ Compact Fluorescent Performance Series Reflector Trims

UniFrame™ Frame-In Kit					
	Vertical Open	Vertical Wall Wash - Single	Vertical Wet Location Clear Lens	Vertical Wet Location Fresnel Lens	Vertical Wet Location Opal Lens
<b>2001F13U</b> 13w Quad/Triple GX24q-1 Base 120v – 0.13amp max 277v – 0.06amp max	2001CL 2001CD 2001WH	2001CLSW 2001CDSW 2001WHSW	2001CLC 2001CDC 2001WHC	2001CLF 2001CDF 2001WHF	2001CLO 2001CDO 2001WHO
<b>2001F18U</b> 18w Triple GX24q-2 Base 120v – 0.16amp max 277v – 0.07amp max					

#### Features

- 1. Mounting Frame: .036" (#20ga.) Galvanized Steel. Accommodates all ceilings up to 1-1/2" thick; including existing or inaccessible areas.
- 2. Trim Clips: "Push In / Twist Out" Stainless Steel clips hold reflector flush to ceiling.
- 3. Junction Box: 2" x 4" x 3-1/2" (22cu.in.) .032" (#22ga.) galvanized steel. UL Listed for maximum of 8 (#12ga.) through branch circuit conductors.
- 4. UniFrame™ Mounting System Grid Ceiling: Tool free mounting in grid ceilings. .036" (20ga.) Galvanized Steel interlocking slide bars adjust to 24-1/8" long accommodating 24" O.C. Ceiling Grid. Adjustable speed clamps for positive attachment to grid ceiling systems.
- 5. UniFrame™ Mounting System Wood Joist Ceiling: Integral nailing tabs, alignment guides, fastener holes and bendable strapping guides for wood joist installation. Galvanized Steel interlocking slide bars adjust from 12-15/16" to 24-1/8" long to accommodate 16" and 24" O.C. joist spacing, with or without strapping.
- 6. Ballast: 120V 277V UL Listed Electronic Ballast, end of lamp life
- protection, class "P" thermally protected, class "A" sound rating.
- 7. Socket: Four-pin base, molded thermoplastic socket, prewired with No. 18 AWM leads to ballast.
- 8. Socket Housing: .036" (#20ga.) Galvanized Steel housing attaches to reflector trim by spring clip for precise optic alignment.

Labels: cULus Listed. Suitable for Damp Locations.

Accessories: 1967A Extra Thick Ceiling Adapter (up to 2" thk)

# (s) ignify

© 2019 Signify Holding. All rights reserved. This document may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners. Signify North America Corporatio 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008