PHILIPS

Suspension light

myLiving

SANDALWOOD 60cm

white

40917/31/CN



Create the right light style

Bring stunning effects to your living room. With a suspension light that adds a touch of modern playfulness, both with the light on and off.

Designed for your living- and bedroom

- Perfect to relax and socialise
- Create a stylish and welcoming atmosphere
- High quality materials
- Create beautiful light effects
- Easy to assemble

Highlights

Perfect to relax and socialise
The living room is the heart of any home - a place where families gather to relax and guests socialise. Lighting for your living- and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and to give the room a warm and welcoming feel.

Create a stylish atmosphere
This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

High quality materials
This lamp is sculpted from layered patterns of high quality materials with superior finishing. This ensures a solid and long lasting product which will enhance your home for many years to come.

Beautiful light effects
The design of this lamp creates beautiful light effects to enhance the atmosphere of your living space in the evening. The intriguing interplay of light and shadow will transform the room when switched on.

Easy to assemble
The compact, modular elements slot together in minutes, and are easy to transport, carry and install.

Specifications

Design and finishing
- Color: white
- Material: fabric

Miscellaneous
- Especially designed for: Living- & Bedroom, Living- & Bedroom
- Style: Contemporary
- Type: Suspension light
- EyeComfort: No

Product dimensions & weight
- Height maximum: 198 cm
- Height minimum: 48 cm
- Length: 60 cm
- Net weight: 0.780 kg
- Width: 60 cm

Service
- Warranty: 2 year(s)

Technical specifications
- Lifetime up to: 15,000 hour(s)
- Mains power: Range 220 V - 240 V, 50-60 Hz
- Fixture dimmable: No
- LED: No
- Built in LED: No
- Energy class included light source: no bulb included
- Fixture is compatible with bulb(s) of class: A++ to E
- Number of bulbs: 1
- Fitting/cap: E27
- Wattage bulb included: -
- Maximum wattage replacement bulb: 40 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated
- Light source replaceable: Yes

Packaging dimensions and weight

- EAN/UPC - product: 6947830438877
- Net weight: 0.780 kg
- Gross weight: 1.470 kg
- Height: 284.000 mm
- Length: 111.000 mm
- Width: 281.000 mm
- Material number (12NC): 915005695301

Issue date: 2023-11-08
Version: 0.223

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com