

PHILIPS

Suspension light

myLiving

Roseval

clear

40966/60/CN



Make a brilliant impression

Bring stunning effects to your living room with a suspension light that adds a touch of modern playfulness, with the light either on or off.

Designed for your living- and bedroom

- Perfect to relax and socialise
- Create a stylish and welcoming atmosphere
- Create beautiful light effects
- Easy to assemble
- High quality materials

Highlights

Perfect to relax and socialise

The living room is the heart of any home – a place where families gather to relax and guests socialise. Lighting for your living- and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and to give the room a warm and welcoming feel.

Create a stylish atmosphere

This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define the localised ambiance you have always desired.

Beautiful light effects

The design of this lamp creates beautiful light effects to enhance the atmosphere of your living space in the evening. The intriguing interplay of light and shadow will transform the room when switched on.

Easy to assemble

The compact, modular elements slot together in minutes, and are easy to transport, carry and install.

High quality materials

This lamp is made of high quality materials with superior finishing. This ensures a solid and long lasting product which will enhance your home for many years to come.

Specifications

Design and finishing

- Color: clear
- Material: synthetics

Miscellaneous

- Especially designed for: Living- & Bedroom, Living- & Bedroom
- Style: Contemporary
- Type: Suspension light
- EyeComfort: No

Product dimensions & weight

- Height maximum: 201.7 cm
- Height minimum: 51.7 cm
- Length: 63 cm
- Net weight: 2.780 kg
- Width: 63 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Mains power: Range 220 V – 240 V, 50–60 Hz
- Fixture dimmable: Yes
- LED: No
- Built in LED: No
- Energy class included light source: no bulb included
- Fixture is compatible with bulb(s) of class: A++ to E
- Number of bulbs: 1
- Fitting/cap: E27
- Wattage bulb included: –
- Maximum wattage replacement bulb: 40 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: I – earthed
- Light source replaceable: Yes

Packaging dimensions and weight

- EAN/UPC - product: 6947830438556
- Net weight: 2.780 kg
- Gross weight: 4.250 kg
- Height: 699.000 mm
- Length: 241.000 mm
- Width: 291.000 mm
- Material number (12NC): 915005634001



Issue date: 2023-11-08
Version: 0.185

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com