

# PHILIPS

Suspension light

myLiving

41231 Apollo

white

41231/31/CN



## Create the right light style

Bring stunning effects to your living room. With a suspension light that adds a touch of modern playfulness, both with the light on and off.

### Special characteristics

- Adjustable height

### Designed for your living- and bedroom

- High quality materials

### Easy to experience

- Retrofittable for a convenient change of lamps.

# Highlights

## Adjustable height



This Philips light is delivered with long cables to offer you a maximum flexibility during installation. Choose the perfect height matching your needs.

## High quality materials

This lamp is sculpted from layered patterns of high quality materials with superior finishing. This ensures a solid and long lasting product which will enhance your home for many years to come.

## Easy lamp replacement

# Specifications

## Design and finishing

- Color: white
- Material: metal

## Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Expressive
- Type: Suspension light
- EyeComfort: No

## Power consumption

- Energy Efficiency Label (EEL): no bulb included

## Product dimensions & weight

- Height maximum: 150 cm
- Height minimum: 50 cm
- Length: 40 cm
- Net weight: 2.160 kg
- Width: 40 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Mains power: Range 220 V – 240 V, 50–60 Hz
- Fixture dimmable: No
- LED: No
- Built in LED: No
- Energy class included light source: no bulb included
- Fixture is compatible with bulb(s) of class: A++ to E
- Number of bulbs: 1
- Fitting/cap: E27
- Wattage bulb included: -
- Maximum wattage replacement bulb: 10.5 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

## Packaging dimensions and weight

- EAN/UPC - product: 6947830439157
- Net weight: 2.160 kg
- Gross weight: 3.500 kg
- Length: 0.000 mm
- Width: 0.000 mm
- Material number (12NC): 915005722801



Issue date: 2020-07-28  
Version: 0.142

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.