







Selenium LED BGP340

Mounting instructions

Instructions de montage
Montagenleitung
Montage instruktie
Istruzioni di montaggio



Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergesi
Monteringsinstruktioner
Instrukcja montazu



LEDs

~220V...240V
50/60Hz



IP66

IK08

6-12 m



LUMEN FLUX

W






max

min

Inrush current

LED37	3S/740	3700	29	11,7	45	-30	65A/100µs
LED42	3S/740	4200	34	11,7	45	-30	65A/100µs
LED55	3S/740	5520	44	11,7	45	-30	80A/150µs
LED74	3S/740	7360	59	11,7	45	-30	80A/150µs
LED92	3S/740	9200	79	11,7	45	-30	80A/150µs
LED110	3S/740	11040	94	11,7	45	-30	80A/150µs



Disconnect before servicing!

The lightsource contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person!

© 2018 Signify Holding.
All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding.
The Netherlands



4427 100 66647
© 11/2018 Signify Holding. All rights reserved

Printed in Hungary
Data subject to change without notice
Keep for future reference: www.philips.com/lighting

