

HADCO


by @signify

Landscape

Decklyte

CUL20 Copper

Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____



Ordering Guide

Example: CUL20

Product Code	CUL20	Copper Decklyte
--------------	-------	-----------------

Specifications

HOUSING:

Spun solid copper. Copper back plate.

FINISH:

Natural Copper is bright polished, untreated copper. Color will age naturally to a fine dark copper patina.

OPTICAL ASSEMBLY:

Reflective white powdercoat on underside of roof.

LAMPING:

12W maximum wedge base T3-¼ lamp. 10W wedge base T3 ¼ (xenon) lamp is included with fixture. Xenon lamp life is approximately 10,000 hours. Lamp does not need to be protected and can be directly handled.

ELECTRICAL ASSEMBLY:

Wedge base socket type (T3-¼ or T5). 12 volt fixture is pre-wired with 6-ft. pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

INSTALLATION & MOUNTING:

Two (2) Stainless #8 wood screws (supplied) via key slots.

WARRANTY:

Ten-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height :

2 9/16" (65mm)

Width:

4" (102mm)

Depth:

1 3/4" (52mm)

Max. Weight:

0.30 lb

@signify