


by (signify

Outdoor

Poles and Brackets

P1566 Straight Round Fluted



Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Order guide

example: P1566 8 A T D

Product Code Pole Height Finit		inish		Outlet Location		Outlet Options	
P1566	8' 10' 12'	A B G H J	Black White Verde Bronze Green	T B	12" Down from Top - Aligned with House Side 4" Up from Top of Base - Aligned with House Side	D G	Standard Duplex GFI Duplex

Note: Top outlets not available with the HFP arms. EPA values based on destructive break testing. For AASHTO ratings, contact factory.

Pole Data

Pole Model	Pole Shape	Pole Type	Shaft Dimension	Pole Fluted	Anchor Base Shape	Bolt Circle Base Dim (i		Hand Hole Dim (in)
P1566	Round	Straight	3	Fluted	square	9.375	8.25 x 27.375	3 x 5

Pole Family	Catalog Number	Nominal Height (ft)	Tenon Section (in)	Wall Thickness (in)	EPA Rating 80 MPH (sq. ft)	EPA Rating 100 MPH (sq. ft)	Anchor Bolts (in)
P1566	P1566-8	8	3	0.125	9.77	5.72	1/2-15 1/2 bs
P1566	P1566-10	10	3	0.125	7.85	4.51	1/2-15 1/2 bs
P1566	P1566-12	12	3	0.125	6.50	3.65	1/2-15 1/2 bs

Specifications

HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy. 319 Permanent mold aluminum. 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel. Tenon is 356 HM sand cast aluminum.

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:


Please visit **www.signify.com/warranties** for more details on structural and finish warranty.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dualfunction indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

P1566 Poles and Brackets

Straight Round Fluted



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

Signify

© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

200 Franklin Square Drive, Somerset, NJ 08873 Felephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S: Telephone 800-668-9008