
HADCO

by signify

www.hadco.com

INSTALLATION INSTRUCTIONS: WAMT14 FLOODLIGHT



The following lamps may be used in this fixture:
50W GY6.35 T-4 Bi-pin
35W GY6.35 T-4 Bi-pin

⚠ SAFETY WARNING:

ALWAYS TURN FIXTURE OFF/DISCONNECT POWER AND ALLOW TO COOL BEFORE PERFORMING ANY MAINTENANCE, INCLUDING RELAMPING AND CLEANING!

This fixture can become very HOT! The fixture housing and lens, especially if it is glass, can become hot enough to blister hands. Attention should be paid to where the fixture is mounted, particularly if it can be touched by children or pets. To help prevent premature failure, decreased performance, overheating and risk of fire, keep fixture and lens clean and free of leaves, mulch, debris and mineral deposits from water. The fixture and lens can be cleaned using a soft cloth and a solution of mild liquid soap and warm water. Wipe clean and dry with a soft, lint-free dry cloth. Avoid polishing fixture or lens.

FOR USE ONLY WITH LINE VOLTAGE LANDSCAPE LIGHTING POWER UNITS THAT ARE RATED MAXIMUM 120 VOLTS PER CIRCUIT.

Do not install fixture within 10 feet (3.05 meters) of a pool, spa or fountain.

This fixture is intended for installation in accordance with the National Electrical Code and local code specifications. Failure to adhere to these codes and instructions may result in serious injury and/or damage to the ballast and void the warranty. These instructions do not purport to cover all details or variations in equipment, nor to provide for every possible contingency related to installation, operation, maintenance, or mounting situation. Should specific problems occur that are not addressed by these instructions, contact your Sales Representative or distributor for assistance. Retain these instructions for future reference.

Signify North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873, USA
Phone: 855-486-2216

Signify Canada Ldt./ Signify Canada Ltée
281 Hillmount Road
Markham ON, Canada L6C 2S3
Phone: 800-668-9008

32001330, revision F

HADCO

by signify

INSTALLATION INSTRUCTIONS

1. Make sure power is turned OFF before installing or servicing this fixture.
2. This fixture must be mounted to a junction box or mounting stake that is UL Listed for line voltage. Mounting stakes S3, M0028A, or junction box TM2H, TMC2H, BI1, BI2, BI3, BI4 may be used.
3. Insert wires through 1/2-14 NPS hole of mounting device and screw fixture onto junction box lid/stake cap.
4. Wire the fixture as follows, using wire nuts to make the splices inside the junction box.
   -Connect white (positive) supply wire to white fixture wire.
   -Connect black (negative) supply wire to black fixture wire.
   -Connect green (ground) supply wire to green fixture wire.
5. Secure the junction box lid/stake cap back onto the junction box/mounting stake.
6. Loosen shroud screws and remove shroud by pulling off of housing.
7. Install specified lamp (not included).
8. Push shroud completely back into housing and tighten shroud screws to secure shroud in place.
9. Loosen screw in arm, aim fixture as desired and tighten screw.
10. Turn power ON.

INSTRUCTIONS PERTAINING TO A RISK OF FIRE OR INJURY TO PERSONS
IMPORTANT SAFETY INSTRUCTIONS - SAVE THESE INSTRUCTIONS!

WARNING - Lamp gets HOT quickly! To reduce the risk of FIRE OR INJURY TO PERSONS:
Do not operate fixture with a missing or damaged lens/lens assembly.
Contact only switch or plug when turning fixture on or off. Do NOT touch hot lens or housing.
Turn off or unplug fixture and allow to cool before relamping. Keep lamp away from combustibles.
Do NOT touch lamp with bare hands at any time; use a soft cloth as oil from skin may damage lamp.