

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: P9400 10 A T D

Product Code	P9400	
<b>Pole Height</b>	10	10'
	12	12'
	14	14'
	16	16'
<b>Finish</b>	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green
<b>Outlet Location (Optional)</b>	T	12" Down from Top - Aligned with House Side
<b>Outlet Options (Optional)</b>	D	Standard Duplex
	G	GFI Duplex

### Specifications

**HOUSING:**

356-T6 Sand Cast Aluminum. 6063-T6 Extruded aluminum . Anchor rods are hot dipped galvanized steel .

**FINISH:**

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

**WARRANTY:**

Three-year limited warranty.

**OUTLET:**

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# P9400 P9400

## Pole

### Specifications

---

**Tenon/Top:**  
3" OD

**Bolt Circle:**  
8" - 9"

**Anchor Rods:**  
(4) 3/4" dia. x 19"

**Base Dimensions:**  
9" sq.

**Hand Hole :**  
2" x 4" Oval

**Shaft:**  
5" to 3" Tapered

**Wall Thickness:**  
0.125 Aluminum

**Height :**  
10', 12', 14', 16'

### Pole EPA Values

---

Windspeed(mph)	Height			
	10'	12'	14'	16'
80	11.2200	9.0300	5.8500	4.6700
100	6.7300	5.2300	3.2300	2.3700

