


PHILIPS

Ledinaire Montat pe suprafață

SM060C



50Hz
60Hz

220V
240V

DURATA DE VIAȚĂ
L65
50 mii ore

IP20


IK03

Max.
40 °C
Min.
10 °C


FIR
INCANDESCENT
650 °C



	Flux luminos sistem	CCT	Balast	P(W)	kg
SM060C LED34S/840 PSU W20L120 NOC	3400lm			34	2.62
SM060C LED40S/840 PSU W20L120 NOC	4000lm	4000K	PSU	40	2.62
SM060C LED34S/840 PSU W20L120 OC	3400lm			34	2.78



Curent de pornire



	LED34S	LED40S
Caracteristici electrice		
I _{max} (A)	10.8	9,68
T _{ref} (μs)	36	75
MCB	Corpur de iluminat Max.	
B-10A	15	15
B-16A	24	24
C-10A	25	25
C-16A	41	41



- Corpul de iluminat va fi montat de un electrician calificat, și cablat în conformitate cu cele mai recente regulamente electrice IEE sau cu cerințele naționale.
- Sursa luminoasă și balastul din acest corp de iluminat nu vor fi înlocuite.



ATENȚIE
RESPECTAȚI MĂSURILE DE
PRECAUȚIE PENTRU MANIPULARE
DISPOZITIVE VULNERABILE LA
DESCĂRCĂRI ELECTROSTATICE

