


PHILIPS

TrueLine

SM530P EL



220 V
240 V

50Hz
60Hz

4A
MAX.

IP40

IK02

GLO W
WIRE
650 °C

Max.
40 °C
Min.
10 °C



Surface
Mounted

A

B

C

D



Standalone

1449

1031


200

219


5.1

Surface Mounted

Dimensions in mm



Inrush current



I _{max} (A)	21
T _{ref} (μs)	280
Condition: Input voltage 220V	
MCB	Luminaires Max.
B-10A	15
B-13A	19
B-16A	24
B-20A	30
B-25A	37
C-10A	24
C-13A	32
C-16A	40
C-20A	49
C-25A	62

