

PHILIPS

Spot light

myLiving

Runner

white



53092/31/12



High quality spot lamp without bulb

This industrial style double spot is small, slim and simple and fits perfectly into any modern interior. The white aluminum housing complements the light source flawlessly. A striking decorative item with a rotating light source.

Superior design for an optimal light effect

- Adjustable spot head for maximum flexibility



Highlights

Easy-to-adjust spot head

The adjustable spot head is designed to direct the light where you need it most.

Specifications

Design and finishing

- Color: white
- Material: metal

Extra feature/accessory incl.

- Adjustable spot head: Yes
- Defined light beams: Yes
- Mount product out of arms reach: Yes

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Modern
- Type: Spot light
- EyeComfort: No

Product dimensions & weight

- Height: 10.9 cm
- Length: 30.5 cm
- Net weight: 0.825 kg
- Width: 9.0 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: No bulb included
- Mains power: 50-60 Hz, Range 220 V - 240 V
- Fixture dimmable: Yes
- LED: No
- Built in LED: No
- Energy class included light source: no bulb included
- Fixture is compatible with bulb(s) of class: A++ to E
- Number of bulbs: 2
- Fitting/cap: GU10
- Wattage bulb included: -
- Maximum wattage replacement bulb: 20 W
- IP code: IP20
- Class of protection: I - earthed
- Light source replaceable: Yes

Design and finishing

- Color: white
- Especially designed for: Living- & Bedroom
- EAN/UPC – product: 8718291487944
- Warranty: 2 year(s)
- Net weight: 0.825 kg
- Material: metal
- Style: Modern
- Gross weight: 0.945 kg
- Adjustable spot head: Yes
- Type: Spot light
- Height: 31.600 cm
- Height: 10.9 cm
- EyeComfort: No
- Length: 10.200 cm
- Width: 10.900 cm
- Material number (12NC): 915004328901
- Length: 30.5 cm
- Net weight: 0.825 kg
- Width: 9.0 cm
- Defined light beams: Yes
- Total lumen output fixture: No bulb included
- Mains power: 50–60 Hz, Range 220 V – 240 V
- Fixture dimmable: Yes
- LED: No
- Built in LED: No
- Energy class included light source: no bulb included
- Fixture is compatible with bulb(s) of class: A++ to E
- Mount product out of arms reach: Yes
- Number of bulbs: 2
- Fitting/cap: GU10
- Wattage bulb included: –
- Maximum wattage replacement bulb: 20 W
- IP code: IP20
- Class of protection: I – earthed
- Light source replaceable: Yes



Issue date: 2023-11-08
Version: 0.489

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com