

LUMEC

Inspired by movement

Roadway

Capella



Capella

LED luminaires

Inspired by the splendor of movement, the Lumec Capella LED architectural roadway luminaires blend seamlessly into soft architectural urban and roadway surroundings, as well as more rectilinear settings. With graceful curves and sweeping lines, it contributes to the beautification of any environment and enhances the visual impact of any project. The Capella comes in two sizes to maximize its potential and appeal. The smaller version is perfect for lighting alleyways, pathways, sidewalks and small roadways while the larger version is ideal for city streets and boulevards. The two complement each other and can be used in tandem to add a measure of grace and fluidity to any area, big or small.

Benefits

- Pure lines with high visual appeal.
- Two sizes, offering solutions for a wide range of applications.
- Adaptable luminaires available with various bracket and pole options including curved poles to complement your project
- Exceptional durability & reliability.
- Multiple lumen packages with output of up to 20,800 lumens.
- Type 2, 3, 4, & 5 optics available.
- Highly efficient IP66 optics are protected from the elements and ensure optimal photometric performance.
- Color temperatures 4000K and 3000K are available.
- Dimming driver is standard.
- Maximizes energy savings with multiple driver options and programmed dimming options.




Medium luminaire



CPLM

Dimensions



CPLM

EPA: 0.83 sq. ft.
Weight: 55 lbs (25 kg)

Lumen range: 6,500-20,800 lm

Wattage range: 54-163 W

Efficacy range: 111-139 lm/W



Lumen range: 1,400–10,900 lm

Wattage range: 13–81 W


Efficacy range: 108–138 lm/W

Small luminaire



CPLS

Dimensions



CPLS


EPA: 0.47 sq. ft.
Weight: 30 lbs (13.6 kg)

Enhance the visual impact of your project

See how **Lumec Capella LED** architectural roadway luminaires are as tough and practical as it is beautiful.

Visit [signify.com/prolighting](https://www.signify.com/prolighting) for more information.

Prior to ordering, consult specification sheets for the most current information, notes, and exclusions.





© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corp.
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.