

Outdoor

Poles and Brackets





P195 Straight Round Smooth

Project:	
Location:	
Cat.No:	
Type:	
Lamps:	Qty:
Notos:	

example: P195 12 A T D

Order guide

Product Code P195	Pole Height	Finish		Outlet Location		Outlet Options	
P195	12' 14' 15' 16' 18' 20'	A B G H I J	Black White Verde Bronze Gray Green	Т	12" Down from Top - Aligned with House Side	D G	Standard Duplex GFI Duplex

EPA values based on destructive break testing. For AASHTO ratings, contact factory.

Pole Data

Pole Model	Pole Shape	Pole Type	Shaft Dimension	Pole Fluted	Anchor Base Shape	Bolt Circle	Base Dim (in)	Hand Hole Dim (in)
P195	Round	Straight	4	Smooth	round	7.5 to 9.5	11.5 x 2.375	2 x 4

Catalog Number	Nominal Height (ft)	Tenon Section (in)	Wall Thickness (in)	EPA Rating 80 MPH (sq. ft)	EPA Rating 100 MPH (sq. ft)	Anchor Bolts (in)	
P195-12	12	4	0.188	6.45	3.88	3/4-19 bs	
P195-14	14	4	0.188	4.13	2.31	3/4-19 bs	
P195-15	15	4	0.188	3.92	2.01	3/4-19 bs	
P195-16	16	4	0.188	3.35	1.8	3/4-19 bs	
P195-18	18	4	0.188	2.72	1.34	3/4-19 bs	
P195-20	20	4	0.188	2.17	0.93	3/4-19 bs	

Specifications

HOUSING:

413F, Low-Copper cast aluminum. 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel.

FINISH

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:


Please visit **www.signify.com/warranties** for more details on structural and finish warranty.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dualfunction indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

P195 Poles and Brackets

Straight Round Smooth



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereor is disclaimed. All trademarks are owned by Signify Holding or their respective owners. Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Talanhona 800-668-9008