PHILIPS Ocean Led Bollard BGP708
























led color	ledgine	W +/-10%	kg	* Max.							
740	GRN10	10	8.5	23							
740	ECO18	17	8.5	23							
830	GRN9	10	8.5	23							
830	ECO17	17	8.5	23							
*Maxi	number o	of lumina	aire on I	MCB 16A typ	e B						




















































Disconnect before servicing
Mettre hors tension avant intervention
Offnen nur spannungsfrei
Demonteren voor onderhoud
Togliere tensione prima di fare manutencione
Desconectar antes de manipular
Bryt strömmen före lampbyte







© 2016 Koninklijke Philips N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent - or other industrial or intellectual property rights.

Philips Lighting B.V. The Netherlands