

PHILIPS

Table lamp

66129 iCarePie

white

LED



66129/31/R3



Advanced desk lighting for a brighter future

Philips iCarePie LED desk light creates a well-illuminated learning environment for your productivity. Designed with a 40-min timer feature to remind you of taking breaks and an auto brightness calibration feature for the optimal reading environment, iCarePie creates a brighter way of working for the comfort of your eyes.

Ease of use

- Flexibility to direct light where you need it the most
- Easy intensity control

Energy saving

- Built-in LED, as part of the system

Designed for your home office

- Directed light, perfect for task lighting

Control

- Multi-level step dimming

Highlights

Flexible directional light



This product allows you to adjust the light to any direction that you like.

Easy intensity control



Easy light level adjustability

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Perfect for task lighting



This Philips desk lamp casts bundled light that provides even illumination on the working area.

Multi-level step dimming

Intuitive multi-level brightness control setting gives you great control over your lights and to create the light ambiance that you need.

Specifications

Design and finishing

- Color: white
- Material: aluminium

Extra feature/accessory incl.

- FFP - Frustration Free Pack: Yes

Miscellaneous

- Especially designed for: Home office & Study, Living- & Bedroom
- Type: Table lamp
- EyeComfort: No

Product dimensions & weight

- Height: 40 cm
- Length: 40.1 cm
- Net weight: 1.313 kg
- Width: 18.5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 920 lm
- Mains power: Range 100 V - 240 V, 50-60 Hz
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: -
- Maximum wattage replacement bulb: 9.6 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC - product: 8718696174494
- Net weight: 1.313 kg
- Gross weight: 1.715 kg
- Height: 68.000 mm
- Length: 220.000 mm
- Width: 490.000 mm
- Material number (12NC): 915005862101



Issue date: 2021-11-28
Version: 0.208

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com