

# LIGHTOLIER

by signify

Downlighting

Calculite LED

VP Vandal proof trim



## Experience the change, see the difference

Architectural decorative vandal proof ring combines the impact resistance you need with aesthetics you want.

### Benefits

Calculite's vandal proof trim accessory is strength with a decorative feel. The sleek machined aluminum ring provides aesthetics fit for architectural spaces while providing the rigidity and impact resistance needed for the most demanding applications. The solid aluminum construction with clear polycarbonate lens lock in place to deter tampering, and provide Calculite trims with an IK10 impact rating.

# VP Calculite LED

## Vandal proof trim downlighting



### Features

**Apertures:** 4" & 6" round  
**Finish:** White  
**Reflectors:** Suitable for use with any finish (must use flangeless trim option)  
**Lumens:** 4" in 500–3000lm; 6" in 1000–6000lm  
**Construction:** Machined alluminum. 9034HO Lexan optical grade polycarb lens  
**Impact Protection:** IK10 (20 joule impact protection).  
**Ingress Protection:** IP65, suitable for wet locations  
**Locking:** Locks in place with discrete setscrew located on side of the ring  
**Installation:** Mounted to frame with hardware, bayonet style twist on trim installation

**Frame** Complete luminaire = Frame + Engine + Trim

example: **C4RNLC**

Series	Aperture	Installation	Options
C4 Calculite LED 4"	R Round	N New construction (Non-IC)	— Universal 120/277V 3 347V (specify for Power Over Ethernet) 3IP 347V w/Interact Pro
C6 Calculite LED 6"		R Remodeler (Non-IC)	LC Chicago Plenum IP Interact Pro
		A AirSeal (IC)	— N/A

### Engine

example: **C4L15835NZ10U**

Series	Aperture	CRI	CCT	Beam	Dimming	Options
C4 Calculite LED 4"	05 500lm 10 1000lm 15 1500lm	20 2000lm 25 2500lm 30 3000lm	8 80CRI 9 90CRI	27 2700K 30 3000K 35 3500K 40 4000K	N Narrow M Medium W Wide	Z10 0-10V 1% D Dali L Lutron EcoSystem (Other controls options available, see specification sheets for details.)
C6 Calculite LED 6"	10 1000lm 15 1500lm 20 2000lm 25 2500lm	35 3500lm 48 4800lm 60 6000lm				U Universal (120/277/347V)

### Trim

example: **C4RDLCCF**

Series	Aperture	Style	Finish	Flange
C4 Calculite LED 4"	R Round	DL Downlight	CL Specular clear	F Flangeless
C6 Calculite LED 6"		WW Open Wall Wash	CC Comfort clear	
		LW Lensed Wall Wash	CD Comfort clear diffuse	
		CW Corner Wall Wash	CZ Champagne bronze	
		DW Double Wall Was	BK Black (matte)	
			WH White (matte)	

\* Impact Protection Rating is a scale of 0-10 used to measure a product's ability to withstand physical impact.



Visit [Signify.com/warranties](https://www.signify.com/warranties) for more information on Signify's standard 5-year limited warranty.

See Calculite LED specification sheets for additional drawings and technical information.

