

PHILIPS

Reflector

LED

14W-120W

E27

Warm White

6922341906091



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- No visible flicker

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- A simple LED for everyday use

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E27
- Technology: LED

Bulb dimensions

- Height: 13.3 cm
- Weight: 0.184 kg
- Width: 12.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 25 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 1050 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 110 mA
- Efficacy: 85 lm/W

Packaging information

- EAN: 6922341906091
- EOC: 692234190609100
- Product title: LED 14-120W PAR38 827 25D

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 14 W
- Wattage equivalent: 120 W
- Energy Efficiency Label (EEL): A+

Product dimensions & weight

- Length: 13.3 cm

Rated values

- Rated beam angle: 25 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 1050 lumen
- Rated peak intensity: 5000 cd
- Rated power: 14 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 6922341906091
- Net weight: 0.385 kg
- Gross weight: 0.482 kg
- Height: 13.700 cm
- Length: 12.500 cm
- Width: 12.500 cm
- Material number (12NC): 929002339107



Issue date: 2021-01-11
Version: 0.26

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com