


PHILIPS

Ceiling light

myLiving

CL850

Dim



6947830439935



Set your desired ambiance at your fingertips

Create the right ambience every time. Our all-in-one Premium ceiling light gives you a sophisticated yet easy-to-use remote control to select different light settings while managing multi-layer light changes. With its attractive design, you can set the scene in style

Easy to experience

- Enhance your moment Tunable with memory function
- 10s time delay light off with remote control

Light effect

- Multiple layered visual effect Dynamic tiered design

Premium quality

- Premium faceted crystals for sparkling light effect

Control

- 4 pre-set scenes

Highlights

Enhance your moment Tunable with memory function

Memorize your favorite tunings of different light settings to easily find your perfect level of illumination.

10s time delay light off with remote control

The 10 second delay gives you time to leave the room once you've turned out the light with your remote.

Multiple layered visual effect Dynamic tiered design

This dynamic tiered design makes for a striking impression that adds a creative touch to your rooms.

Premium faceted crystals for sparkling light effect

Faceted crystals a touch of refined, vintage charm to your space.

4 pre-set scenes

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

Specifications

Design and finishing

- Color: aluminium
- Material: Aluminium

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Functional
- Type: Ceiling light

Packaging dimensions and weight

- Net weight: 3.800 kg

Product dimensions & weight

- Height: 8 cm
- Length: 65 cm
- Net weight: 3.8 kg
- Width: 65 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Diameter: 650 mm
- Total lumen output fixture: 4200
- Light color: 2700-6500
- Mains power: 220-240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 52
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- Gross weight: 6.330 g
- Height: 0.000
- Length: 0.000
- Width: 0.000
- Material number (12NC): 915005771301



Issue date: 2023-11-08
Version: 0.174

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com