


PHILIPS

StoreSet Trunking EL version

SM505S



Lumen package	P (W)	P (W)		Driver			Optics				m ²	kg	
		Type	Max.	PSU	PSD	A20	DA25N	DA25W	DA35W	DA45			MB
LED66S	830	53	55										
	840	49	51										
LED80S	830	66	69	0.1	2.6
	840	61	63										
LED90S	830	77	80										
	840	70	73										


! The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.

! Caution, risk of electric shock. The light source of this luminaire is not replaceable, when the light source reaches its end of life the whole luminaire shall be replaced. The driver shall only be replaced by the manufacturer or his service agent or a similar qualified person.

! The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material.


! DO NOT OPEN

! ATTENTION OBSERVE PRECAUTIONS FOR HANDLING ELECTROSTATIC SENSITIVE DEVICES








Inrush current


	LED66S/LED80S/LED90S	LED66S/LED80S	LED90S
	Xtitanium 75W 0.12-0.4A 220V 230V	Xtitanium 75W 0.12-0.40A 215V TD CL 230V	Xtitanium 100W 0.15-0.5A 300V iXT TD 230V
Electrical characteristics			
I max (A)	22	19	4.5
Tref (µs)	275	280	100
Luminaire max.			
BCM			
B-16 A	24	24	18
	PSU	PSD	PSD





1a



1b







1c





Only use a soft cloth.



Optic A20



1





2

3



Phase selection





©2018 Signify Holding

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Signify Holding.
The Netherlands