




PHILIPS

TrueLine


RC530B EL




			A	B	VPC	PCV	
Recessed	VPC	W8L150	1497	1450	4.3		
Recessed	PCV	W8L145	1472	1450		4.4	
Recessed Line	VPC/PCV	W8L145	1448		4.2		4.5



Optional: RC530Z EP SET WH




Inrush current




$I_{max}(A)$	21
$T_{ref}(\mu s)$	280
Condition: Input voltage 220V	
MCB	Luminaire's Max.
B-10A	15
B-13A	19
B-16A	24
B-20A	30
B-25A	37
C-10A	24
C-13A	32
C-16A	40
C-20A	49
C-25A	62




Recessed




1





Wieland





2




3




PC V




Min.
12 mm




Max.
42 mm



4



5





Recessed Line

