

Philips Mini Koffer EGP 060

Mounting instructions

Instructions de montage

Instrucciones de montaje

Kokoonpano- ja kiinnitysohjeet

Szerelési utasítások

Montageanleitung

Instruções de montagem

Montaj yönergesi

Návod k montáži

Montage instructie

Monteringsinstruktioner

Οδηγίες συναρμολόγησης

Монтажная инструкция

Istruzioni di montaggio

Monteringsvejledning

Instrukcja montażu



		LINE			LED			EL		IK	
	LED	GRN16-2S/830	1600	16	12	●	●	●	●	07	6.2
	LED	GRN20-2S/740	1960	16.8	12	●	●	●	●	07	6.2
	LED	GRN21-2S/657	2080	19.6	16	●	●	●	●	07	6.2
	LED	GRN24-2S/830	2400	22.6	18	●	●	●	●	07	6.2
	LED	GRN29-2S/740	2930	22.9	18	●	●	●	●	07	6.2
	LED	GRN31-2S/657	3120	28.8	24	●	●	●	●	07	6.2
	LED	ECO23-2S/830	2320	23	12	●	●	●	●	07	6.2
	LED	ECO28-2S/740	2840	23.6	12	●	●	●	●	07	6.2
	LED	ECO30-2S/657	3020	27.2	16	●	●	●	●	07	6.2
	LED	ECO35-2S/830	3480	34	18	●	●	●	●	07	6.2
	LED	ECO43-2S/740	4250	35.2	18	●	●	●	●	07	6.2
	LED	ECO45-2S/657	4530	40.2	24	●	●	●	●	07	6.2



Use Philips lamps for optimum performance
 · Fonctionnement optimal avec lampes Philips
 · Optimale Betriebsleistung mit Philips-Lampen
 · Toimii parhaiten Philips-lamppujen kanssa
 · Fungerar bäst med lampor från Philips

· Werkt het best met Philips-lampen
 · Resultados óptimos con lámparas Philips
 · Fungerer mest optimalt med Philips-lamper


· Funzionamento ottimale garantito con lampade Philips
 · Funciona melhor com lâmpadas Philips no interior
 · Fungerer bedst med Philips-lamper

4411 102 67372


© 01/2019 Signify Holding. All rights reserved
 Data subject to change without notice
 Printed in Poland
www.philips.com/lighting

PHILIPS


EGP 060 RETROFIT - EGP 060 UPGRADE










EGP 060 UNIT




LIFE LED MODULE




EGP 060 RETROFIT - EGP 060 UPGRADE




8




9




10





11






12




DII/DI2





DALI





12'





DII/DI2





DII/DI2 SRG10





DALI





DALI SRG10





13





EGP 060 UNIT






→ 28/03/2013








4



x4 → 02/2012
x2 03/2012 →




1 2 3 4 5 6

 $(2Nm)$ 

I2NC 4411 102 67372


4'



CAUTION
Static Sensitive Devices
Do not open outside EDS protected area /
Ne pas ouvrir hors de la zone protégée ESD




4''











CAUTION
Static Sensitive Devices
Do not open outside EDS protected area /
Ne pas ouvrir hors de la zone protégée ESD







LIFE LED MODULE







2'



4411 102 67372

© 01/2019 Signify Holding. All rights reserved
Data subject to change without notice
Printed in Poland
www.philips.com/lighting