

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: P1516 8 A T D

Product Code	P1516	
<b>Pole Height</b>	8	8'
	10	10'
	12	12'
<b>Finish</b>	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green
<b>Outlet Location (Optional)</b>	T	12" Down from Top - Aligned with House Side *1
	B	4" Up from Top of Base - Aligned with House Side
<b>Outlet Options (Optional)</b>	D	Standard Duplex
	G	GFI Duplex

\*1 Top outlets not available with the HFP arms.

### Specifications

#### HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy . 319 Permanent mold aluminum . 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel .

#### FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

#### WARRANTY:

Three-year limited warranty.

#### OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# P1516 P1516

## Pole

### Specifications

---

**Tenon/Top:**  
3" OD

**Bolt Circle:**  
9 3/8"

**Anchor Rods:**  
(4) 1/2" dia. x 15 1/2"

**Base Dimensions:**  
8 1/4" sq. x 27 3/8"

**Base Cover:**  
(Included) 12 3/4" dia. x 5 1/2"

**Hand Hole :**  
3" x 5"

**Shaft:**  
3" Straight

**Wall Thickness:**  
0.125 Aluminum

**Height :**  
8', 10', 12'

### Pole EPA Values

---

Windspeed(mph)	Height		
	8'	10'	12'
80	9.9900	8.0200	6.6400
100	5.8400	4.6000	3.7200

