



Bottom view

Catalogue No.	Finish	Lamp
8109WH	White	20W T4 HMC (M156, C156)
8109BK	Black	GU6.5 TAL base
8109AL	Aluminum	Clear glass

Features

- 1. Track Attachment Fitting:** Molded polycarbonate, rotates into track and locks into place with the use of push tabs. Integral colour.
- 2. Push Tab:** Molded polycarbonate. Locks and detaches unit from track.
- 3. Track Adaptor Housing:** Die-cast aluminum.
- 4. Movable Contact:** Solid brass. Extends for connection to 2nd circuit in Advent track.
- 5. Ballast Housing:** Extruded housing with die-cast aluminum end caps.
- 6. Ballast:** High Power Factor metal halide electronic ballast. Thermally protected, 0.20A maximum input current, 24.5W input power.
- 7. Pivot Mount:** Allows for 350° horizontal with tensioned mounts for controlled aim.
- 8. Lamp Housing:** 0.04" (1.02mm) aluminum.
- 9. Lampholder:** Twist and Lock GU6.5 base allows lamp positioning with a single rotation. 5kV (250V) pulse rated PPS body socket with nickel-plated contacts. 18 AWG silicone leads with fiberglass outer sleeve inside of the lamp housing.
- 10. Reflector (sold separately):** 0.02" (0.51mm) embossed specular anodized aluminum.
- 11. Protective Glass:** 0.13" (3.18mm) tempered glass.
- 12. Housing Cover:** 0.04" (1.02mm) aluminum.
- 13. Knobs:** Steel painted knurled knobs.
- 14. Pivot Mounting:** Allows 180° vertical rotation with tensioned mounts for controlled aim.

Accessories (Sold separately)

- Specular Anodized Reflector T4 Series:
- Clear spot reflector 10°: **24MHT4RS**
 - Clear narrow flood reflector 25°: **24MHT4RNF**
 - Clear flood reflector 35°: **24MHT4RF**
 - Bronze spot reflector 10°: **24MHT4RSCCZ**
 - Bronze narrow flood reflector 25°: **24MHT4RNFCCZ**
 - Bronze flood reflector 35°: **24MHT4RFCCZ**
 - Louver (Hex Cell): **AL35HC**
 - Light frost filter 3-5/16" (84mm): **AF35FR**

Use with accessories holder 8195 sold separately:

- Special Diffusion Filter: **AF25** series
Colour Filters: **ADF25** series

Mounting

For Monopoint, Multipoint, recessed track, suspension track, suspension stems, sloped ceiling adapter, Fast Track and Advent track systems only. Not compatible with ProSpec track systems. Ceiling and horizontal or vertical wall mounts.

Finish

All painted finishes are baked powder or enamel.

Markings

cCSAus Certified for dry locations only.

Canlyte

3015 Louis-Amos, Lachine, Québec H8T 1C4 • (514) 636-0670 • (514) 636-0460

Lightolier

631 Airport Road, Fall River, Ma02720 • (508) 679-8131 • Fax (508) 674-4710
We reserve the right to change details of design, materials and finish.
© 2009 Philips Group

Job Information

Type:

Job Name:

Cat. No.:

Lamp(s):

Notes:

PHILIPS
LIGHTOLIER