

PHILIPS

Halogen bulb

Halogen Classic

53 W (70 W)

E27 cap

Warm white



8718291202646



Sparkling halogen light in a familiar shape

The Philips Halogen Classic range offers familiar light bulb shapes with a sparkling, natural, dimmable light. With a lifetime that is twice that of incandescent bulbs, Halogen Classic halogen bulbs have all your home lighting needs covered.

Superior light quality

- Dimmable
- Sparkling natural light

The economical and ecological choice

- Double the lifetime of a traditional bulb

Highlights

Dimmable

You control the level of light you need. Dimmable with all dimmers, this Philips halogen bulb can be adjusted from a bright, sparkling light to a warm, cosy glow.

Sparkling natural light



This new classic light bulb provides a sparkling, natural halogen light, allowing the full richness of colours in your interior to be seen at their best. Instant brightness, without delay.

Double the lifetime



This lamp lasts twice as long as a standard bulb. So it replaces two lamps, for lower cost and less hassle. The lifetime is based on the average usage of 2.7 hrs per day or 1000 hrs a year.

Specifications

Characteristics

- Dimmable: Yes
- Lamp shape: Non-directional bulb
- Socket: E27
- Technology: Halogen

Lamp dimensions

- Diameter: 56 mm
- Height: 97 mm
- Width: 56 mm

Durability

- Average life (at 2.7 hrs/day): 2 a
- Lumen maintenance factor: 0.8
- Nominal lifetime: 2,000 h
- Number of switch cycles: 8,000

Light characteristics

- Application: Sparkling light
- Beam angle: not applicable degree(s)
- Colour rendering index (CRI): 100
- Colour temperature: 2800 K
- Light Colour Category: Warm White
- Nominal luminous flux: 850 lm
- Starting time: 0 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: not applicable mA

Power consumption

- Power factor: 1
- Voltage: 230 V
- Wattage: 53 W
- Wattage equivalent: 70 W

Rated values

- Rated beam angle: not applicable degree(s)
- Rated lifetime: 2,000 h
- Rated luminous flux: 850 lm
- Rated peak intensity: not applicable cd
- Rated power: 53 W



Issue date: 2023-11-08
Version: 0.539

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com