

PHILIPS

Lamp (Dimmable)

LED

8 W-50 W

E27

Flame

Dimming



8718696575437



Designed to be seen

Introducing the new Philips Vintage LED lamp family, a collection that is reminiscent of familiar incandescent lamps. They stand out when used as a statement piece, adding a sense of nostalgia to your interior.

Choose for a sustainable solution

- Long-life tubes – Lasts up to 15 years
- Saves up to 80% energy

Light beyond illumination

- Vintage style, modern LED technology

Designed to be seen, looks good on and off

- Cord

Highlights

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light tubes and enjoy a perfect lighting solution for over 15 years.

Saves up to 80% energy



Enjoy the energy savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Vintage-style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Cord

This lamp can be used in combination with one of the Philips cords to complete your interior illumination and bring an industrial feel to your living space.

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Technology: LED

Lamp dimensions

- Height: 16.8 cm
- Weight: 0.166 kg
- Width: 12 cm

Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

Light characteristics

- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2200 K
- Light Colour Category: Flame
- Nominal luminous flux: 630 lm
- Starting time: <0.5 s

Miscellaneous

- EyeComfort: No

Other characteristics

- Lamp current: 52 mA
- Efficacy: 78 lm/W

Packaging information

- EAN: 8718696575437
- EOC: 871869657543701
- Product title: LED classic 50W G120 E27 2200K GOLD 1PF

Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage: 8 W
- Wattage equivalent: 50 W
- Energy efficiency label (EEL): A+

Product dimensions and weight

- Length: 16.8 cm

Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 630 lm
- Rated power: 8 W

Technical specifications

- Frequency: 50–60 Hz



Issue date: 2023-11-08
Version: 0.583

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com