

# PHILIPS

Spot

LED

5W (50W)

GU5.3 cap

Cool daylight

Non-dimmable



8718696579572



## Durable LED accent lighting with a focused beam

Philips LED spots provide a focused bright beam, an long life, and significant energy savings.

### Beacon of trust

- You can trust what the Philips packaging is saying.

### Simple replacement

- Get maximum light output as soon as you flip the switch.

### Create an active atmosphere

- Soft sparkling light for modern interior

### Choose for a sustainable solution

- Safe for any room and convenient to recycle

# Highlights

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Instant start

Immediate light when switching on, that is the promise of the Philips instant starting energy saving LED lamps.

## 4000K Bright white light

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

# Specifications

## Bulb characteristics

- Shape: Spot
- Dimmable: No
- Lamp shape: Directional spot
- Socket: GU5.3

## Bulb dimensions

- Height: 46 mm
- Width: 50 mm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Application: Accent light
- Beam angle: 24 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 435 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: 1 s
- Correlated Color Temperature (Nom): 6500 K
- Luminous Efficacy (rated) (Nom): 87.00 lm/W
- Luminous Flux: 435 lumen

## Other characteristics

- Lamp current: 580 mA
- Efficacy: 87 lm/W
- EU RoHS compliant: Yes

## Packaging dimensions and weight

- Net weight: 0.045 kg

## Power

- Power Factor (Fraction): 0.5

## Power consumption

- Power factor: >0.5
- Voltage: 12 V
- Wattage: 5 W
- Wattage equivalent: 50 W
- Power Consumption: 5 W

## Product dimensions & weight

- Length: 4.7 cm

## Rated values

- Rated beam angle: 24 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 435 lumen
- Rated peak intensity: 1700 cd
- Rated power: 5 W

## Technical specifications

- Frequency: 50-60 Hz
- Dimmable: No
- Line Frequency: - Hz
- Cap-Base: GU5.3 | GU5.3

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696579572
- Gross weight: 0.060 kg
- Height: 5.200 cm
- Length: 4.500 cm
- Width: 4.500 cm
- Material number (12NC): 929001240208



Issue date: 2023-11-08  
Version: 0.510

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)