

PHILIPS

Spot (Dimmable)

LED

5W-50W

GU10

Warm White

Dimming

8718696671979



Dimmable LED spot with a focused bright beam

This Philips LED spot provides a dimmable, focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

High quality light

- Provides a bright, crisp light

Choose for a sustainable solution

- Safe for any room and convenient to recycle

Highlights

Provides a bright, crisp light

This GU10 indoor spotlight provides a focused beam of bright, white light.

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them

safe for any room and convenient to recycle.

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Technology: LED

Bulb dimensions

- Height: 5.4 cm
- Weight: 0.05 kg
- Width: 5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 405 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 25 mA
- Efficacy: 81 lm/W

Packaging information

- EAN: 8718696671979
- EOC: 871869667197900
- Product title: LEDClassic 5-50W GU10 830 60D D 1BC/10

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 5 W
- Wattage equivalent: 50 W
- Energy Efficiency Label (EEL): A+

Product dimensions & weight

- Length: 5.4 cm

Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 15,000 h
- Rated peak intensity: 450 cd
- Rated power: 5 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions & weight

- EAN/UPC - product: 8718696671979
- Net weight: 0.052 kg
- Gross weight: 0.071 kg
- Height: 14.600 cm
- Length: 5.200 cm
- Width: 9.000 cm
- Material number (12NC): 929001364419



Issue date: 2023-11-07
Version: 0.75

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com