

# PHILIPS

Bulb

LED

7W-60(60W GLS, 12W CFL)W

B22

Warm White

8718696732441



## A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

### High quality light

- No visible flicker

### Choose a simple replacement for your old bulbs

- Similar shape and size as incandescent globe

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

### Designed to be seen, looks good on and off

- Looks good on and off

# Highlights

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

## Replaces globe incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting LED globe. The perfect sustainable replacement for traditional incandescent globes.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: B22
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 13.5 cm
- Weight: 0.11 kg
- Width: 9.5 cm

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off. "

**Light characteristics**

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 806 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

**Miscellaneous**

- EyeComfort: Yes

**Other characteristics**

- Lamp current: 60 mA
- Efficacy: 115 lm/W

**Packaging information**

- EAN: 8718696732441
- EOC: 871869673244100
- Product title: LEDGlobe 7-60W G95 B22 WW 230V\_AU

**Power consumption**

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7 W
- Wattage equivalent: 60 W

**Product dimensions & weight**

- Length: 13.5 cm

**Rated values**

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lumen
- Rated power: 7 W

**Technical specifications**

- Frequency: 50-60 Hz

**Packaging dimensions & weight**

- EAN/UPC - product: 8718696732441
- Net weight: 0.112 kg
- Gross weight: 0.153 kg
- Height: 12.900 cm
- Length: 9.600 cm
- Width: 9.600 cm
- Material number (12NC): 929002442069



Issue date: 2022-07-19  
Version: 0.155

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)