

PHILIPS

Candle & Lustre
(Dimmable)

LED

6W-40W

B15

Warm Glow

Dimming

8718696766521



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Dims to a warm glow

Designed to be seen, looks good on and off

- Modern style LED

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light..

Modern

Modern design for contemporary interior décor, with a unique sleek design perfect for any home with an industrial-chic feel. It features a smoky grey glass with a thin, single, vertical filament and a black finish base to match your décor. Cooler light output for crisp and clean ambience.

Specifications

Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional candle
- Socket: B15
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 11.3 cm
- Weight: 0.072 kg
- Width: 3.8 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 h
- Number of switch cycles: 50,000

Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200-2700 K
- Light Color Category: Warm Glow
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 822-827 | tunable warm white

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 35 mA
- Efficacy: 78 lm/W

Packaging information

- EAN: 8718696766521
- EOC: 871869676652100
- Product title: LED 6-35W B15 2700K B38 CL WGD 2BC/4

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 6 W
- Wattage equivalent: 40 W

Product dimensions & weight

- Length: 11.3 cm

Rated values

- Rated lifetime: 25,000 h
- Rated luminous flux: 470 lumen
- Rated power: 6 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions & weight

- EAN/UPC – product: 8718696766521
- Net weight: 0.124 kg
- Gross weight: 0.146 kg
- Height: 15.000 cm
- Length: 4.000 cm
- Width: 14.000 cm
- Material number (12NC): 929001140379



Issue date: 2023-11-07
Version: 0.266

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com