

# PHILIPS

Bulb (Dimmable)

LED

6.5W (40W)


E27

Flame

Dimmable



8718696803516



## Designed to be seen

Introducing the new Philips Vintage LED lamp family, a collection that is reminiscent of familiar incandescent bulbs. They stand out when used as a statement piece, adding a sense of nostalgia to your interior.

### High quality light

- Designed for the comfort of your eyes

### Choose for high quality light

- Extra warm light effect

### Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb
- Vintage range
- Cord

### Choose for a sustainable solution

- Long life bulbs – Lasts up to 15 years
- Better for your wallet and your planet

### Light beyond illumination

- Vintage style, modern LED technology

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Extra warm light (2200K)

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## Vintage range

The Philips Vintage collection is available in an array of giant shapes, candles and other familiar form factors, to provide a seamless fit across your space.

## Cord


The Philips bulbs can be used in combination with one of the Philips cords to complete your interior illumination and bring an industrial feel to your living space.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Saves up to 80% energy



LED technology saves up to 80% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

## Vintage style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Transparent Amber

## Bulb dimensions

- Height: 27.3 cm
- Weight: 0.2 kg
- Width: 6.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

**Light characteristics**

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Light Color Category: Flame
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 820 | CCT of 2000K

**Miscellaneous**

- EyeComfort: Yes

**Other characteristics**

- Lamp current: 40 mA
- Efficacy: 72 lm/W

**Packaging information**

- Product family: LED Classic, EyeComfort
- EAN: 8718696803516
- EOC: 871869680351600
- Product title: LED classic-giant 40W E27 T65 GOLD DIM

**Power consumption**

- Power factor: 0.7
- Voltage: 230 V
- Wattage: 6.5 W
- Wattage equivalent: 40 W

**Product dimensions & weight**

- Length: 27.3 cm

**Rated values**

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 470 lumen
- Rated power: 6.5 W

**Technical specifications**

- Frequency: 50 Hz

**Packaging dimensions and weight**

- EAN/UPC – product: 8718696803516
- Net weight: 0.196 kg
- Gross weight: 0.260 kg
- Height: 32.000 cm
- Length: 10.000 cm
- Width: 10.000 cm
- Material number (12NC): 929001873601



Issue date: 2023-11-08  
Version: 0.828

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)