

# PHILIPS

Spot

LED

4.6W-50W

GU10

Warm White

8718696819012



## Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

### High quality light

- Bright white light

### Choose for a sustainable solution

- Safe for any room and convenient to recycle

### Light beyond illumination

- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

## Instant on

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Technology: LED

## Bulb dimensions

- Height: 5.4 cm
- Weight: 0.05 kg
- Width: 5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 410 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 39 mA
- Efficacy: 89 lm/W

## Packaging information

- EAN: 8718696819012
- EOC: 871869681901200
- Product title: LEDClassic 4.6-50W GU10 830 60D 6pack

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 4.6 W
- Wattage equivalent: 50 W

## Product dimensions & weight

- Length: 5.4 cm

## Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 450 cd
- Rated power: 4.6 W

### Technical specifications

- Frequency: 50-60 Hz

### Packaging dimensions and weight

- EAN/UPC - product: 8718696819012
- Net weight: 0.300 kg
- Gross weight: 0.354 kg
- Height: 11.500 cm
- Length: 5.300 cm
- Width: 17.100 cm
- Material number (12NC):  
929001287698



Issue date: 2021-11-29  
Version: 0.31

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)