

# PHILIPS

Spot

LED

4.6W-50W

GU10

Cool White

8718696819036



## Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

### High quality light

- Provides a bright, crisp light

### Choose for a sustainable solution

- Safe for any room and convenient to recycle

### Light beyond illumination

- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Provides a bright, crisp light

This GU10 indoor spotlight provides a focused beam of bright, white light.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

## Instant on

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10

## Bulb dimensions

- Height: 5.4 cm
- Width: 5 cm

## Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 60 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 430 lm
- Warm-up time to 60% light: instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 93 lm/W

## Packaging information

- EAN: 8718696819036
- EOC: 871869681903600
- Product title: LEDClassic 4.6-50W GU10 840 60D 6pack

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 4.6 W
- Wattage equivalent: 50 W

## Product dimensions and weight

- Length: 5.4 cm

## Rated values

- Rated peak intensity: 450 cd

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions & weight

- EAN/UPC - product: 8718696819036
- Net weight: 0.3 kg
- Gross weight: 0.35 kg
- Height: 11.5 cm
- Length: 5.3 cm
- Width: 17.1 cm
- Material number (12NC): 929001287798



Issue date: 2024-02-02  
Version: 0.35

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)