

# PHILIPS

Spot

LED

5W-50W

GU5.3

Cool White

8718696819197



## Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

### Choose for a sustainable solution

- Safe for any room and convenient to recycle

# Highlights

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them

safe for any room and convenient to recycle.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Type of glass: Clear
- Bulb Finish: Clear
- Bulb Material: Glass

## Bulb dimensions

- Height: 4.6 cm
- Width: 5.1 cm

## Design and finishing

- Material: Glass

## Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +40 °C

## Light characteristics

- Beam angle: 60 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 410 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 4000 K
- Luminous Efficacy (rated) (Nom): 82 lm/W
- Luminous Flux: 410 lm

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 82 lm/W
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8718696819197
- EOC: 871869681919700
- Product title: LEDClassic 5-50W MR16 840 60D 6pack

## Power

- Power Factor (Fraction): 0.6

## Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 5 W
- Wattage equivalent: 50 W
- Power Consumption: 5 W

## Product dimensions and weight

- Length: 4.6 cm

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 420 cd

## Technical specifications

- Frequency: 50-60 Hz
- Dimmable: No
- Line Frequency: - Hz
- Cap-Base: GU5.3

## Packaging dimensions and weight

- EAN/UPC – product: 8718696819197
- Net weight: 0.24 kg
- Gross weight: 0.3 kg
- Height: 14.4 cm
- Length: 5.3 cm
- Width: 17.1 cm
- Material number (12NC): 929001280598



Issue date: 2024-02-06  
Version: 0.29

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)