

PHILIPS

Bulb

LED

8 W (60 W)

E27 cap

Cool Daylight / Warm White

8718696827291



One lamp. Your switch. Three light settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED lamp, you can easily change the setting from bright light, to natural light and to a cozy warm glow. All you need is your existing switch.

Create a warm atmosphere

- Three light settings from 2700 K to 2500 K to 2200 K

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- No dimmer or additional installation needed
- Instant on

Highlights

Three light settings

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, cozy light, while those with a higher Kelvin value produce a more energizing light. These new Scene Switch bulbs allow you to switch from functional lighting to natural light and to a cozy, warm dimmed light. Light levels can change from 100% to 40% to 10%. Now you can easily customize your room for a variety of tasks or adapt it to suit your mood.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Plug and play



Does not require any additional installation or a dimmer switch. This bulb is not suitable for use with dimmers. If used on a dimmer set the dimmer setting to 100% brightness.

Instant on

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Type of glass: Frosted

Bulb dimensions

- Height: 11.1 cm
- Width: 6.1 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 100,000

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500/3000 K
- Light Color Category: Cool Daylight / Warm White
- Nominal luminous flux: 880 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 78 mA

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 8 W
- Wattage equivalent: 60 W

Product dimensions & weight

- Length: 11.1 cm

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 880 lumen
- Rated power: 8 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718696827291
- Net weight: 0.060 kg
- Gross weight: 0.084 kg
- Height: 16.600 cm
- Length: 6.200 cm
- Width: 10.000 cm
- Material number (12NC): 929001906369



Issue date: 2023-11-08
Version: 0.514

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com